


TOP VIEW

see Note 7




SIDE VIEW



FRONT VIEW

COMMON DIMENSIONS	
A	0.35 $\pm$ 0.02
A1	0.08 $\pm$ 0.01
A2	0.27 REF
A3	0.040 BASIC
b	$\phi$ 0.21 $\pm$ 0.03
D	0.857 $\pm$ 0.025
E	1.432 $\pm$ 0.025
D1	0.35 BASIC
E1	1.05 BASIC
e	0.35 BASIC
SD	0.175 BASIC
SE	0.175 BASIC
DEPOPULATED BUMPS: NONE	



BOTTOM VIEW

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is  $\pm$  0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.

**maxim**  
integrated™

TITLE  
PACKAGE OUTLINE 8 BUMPS  
ULTRA THIN WLP PKG. 0.35 mm PITCH, Z80B1+1

APPROVAL DOCUMENT CONTROL NO.  
21-100166 REV. A 1/1