







1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5-2009.
3. COPLANARITY APPLIES TO THE TERMINALS AND ALL OTHER BOTTOM SURFACE METALLIZATION.
4. MARKING SHOWN IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE EU ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.
7. PACKAGE CODE: F173B3FY+1.



* CONTROLLING DIMENSION: MM

SYMBOL	MILLIMETER		
	MIN.	NOM.	MAX.
A	0.700	0.750	0.800
A1	0.000	—	0.050
A2	—	0.530	0.580
A3	—	0.203	REF.
b	0.150	0.200	0.250
b1	0.180	0.250	0.300
b2	0.250	0.300	0.350
b3	0.350	0.400	0.450
b4	0.450	0.500	0.550
D	—	3.500	BSC
D2	0.900	1.000	1.100
E	—	3.750	BSC
E2	0.290	0.390	0.490
L	0.300	0.400	0.500
L1	0.400	0.500	0.600
L2	0.450	0.550	0.650
L3	0.500	0.600	0.700
L4	0.780	0.880	0.980
L5	0.950	1.050	1.150
L6	1.100	1.200	1.300
L7	1.250	1.350	1.450
e	—	0.475	BSC
e1	—	0.500	BSC
e2	—	0.525	BSC
e3	—	0.535	BSC
e4	—	0.560	BSC
e5	—	0.575	BSC
K1	—	0.025	BSC
K2	—	0.250	BSC
K3	—	0.925	BSC
K4	—	1.000	BSC
K5	—	1.315	BSC

TOLERANCES OF FORM AND POSITION	
aaa	0.150
bbb	0.100
ccc	0.100
ddd	0.050
eee	0.080
fff	0.100



TITLE:
PACKAGE OUTLINE, 17L, FC2QFN PKG
3.5x3.75x0.75mm

APPROVAL
ZHEN LI

DOCUMENT CONTROL NO.
21-100429

REV. B 1/1

—DRAWING NOT TO SCALE—