







NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5-2009.
3. COPLANARITY APPLIES TO THE TERMINALS AND ALL OTHER BOTTOM SURFACE METALLIZATION.
4. MARKING SHOWN IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE EU ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.
7. PACKAGE CODE: F153A3FY+2.



* CONTROLLING DIMENSION: MM

SYMBOL	MILLIMETER		
	MIN.	NOM.	MAX.
A	0.700	0.750	0.800
A1	0.000	—	0.050
A2	—	0.530	0.580
A3	—	0.203	REF.
b	0.180	0.250	0.300
b1	0.250	0.300	0.350
b2	0.350	0.400	0.450
D	—	3.5	BSC
E	—	3.75	BSC
L	0.450	0.550	0.650
L1	0.490	0.590	0.690
L2	0.525	0.625	0.725
L3	0.550	0.650	0.750
L4	1.100	1.200	1.300
L5	1.405	1.505	1.605
e	—	0.500	BSC
e1	—	0.525	BSC
e2	—	0.575	BSC
e3	—	0.900	BSC
e4	—	0.975	BSC
e5	—	1.325	BSC
K1	—	0.250	BSC
K2	—	0.425	BSC
K3	—	0.450	BSC
K4	—	1.325	BSC
K5	—	0.400	BSC

TOLERANCES OF FORM AND POSITION

aaa	0.150
bbb	0.100
ccc	0.100
ddd	0.050
eee	0.080



TITLE:
PACKAGE OUTLINE, 15L, FC2QFN PKG
3.5X3.75X0.75mm

APPROVAL
YUANYUAN WEN

DOCUMENT CONTROL NO.
21-100624

REV. 1
B

—DRAWING NOT TO SCALE—