





24-Lead Module with Connector Interface [MODULE]

(ML-24-9)

Dimensions shown in millimeters.



UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE:

$$X.XX = \pm 0,15$$
Degrees = $\pm 1.0^\circ$