




TOP VIEW



SIDE VIEW



DETAIL A



BOTTOM VIEW

-DRAWING NOT TO SCALE-

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. N IS THE TOTAL NUMBER OF TERMINALS.
3. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5-2009.
4. COPLANARITY APPLIES TO THE TERMINALS AND ALL OTHER BOTTOM SURFACE METALLIZATION.
5. DIMENSION b APPLIES TO METALLIZED TERMINAL AND IS MEASURED BETWEEN 0.15MM AND 0.30MM FROM THE TERMINAL TIP. IF THE TERMINAL HAS THE OPTIONAL RADIUS ON THE OTHER END OF THE TERMINAL, THE DIMENSION b SHOULD NOT BE MEASURED IN THAT RADIUS AREA.
6. MARKING SHOWN IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
7. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE EU ROHS COMPLIANT WITHOUT EXEMPTION AND Pb-FREE.
8. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.

COMMON DIMENSIONS			
DIM	MIN	NOM	MAX
E	3.500		
D	5.000		
e	0.500		
A	---	0.650	---
M	0.530		
S	0.120		
b	0.200		
aaa	0.100		
ccc	0.100		
ddd	0.080		
N	20		
b1	0.180		
b2	0.346		
b3	1.100		
b4	2.100		
b5	0.670		
b6	0.485		
e1	0.325		
k	0.300		
k1	0.955		
k2	0.790		
k3	0.560		
L	0.400		
L1	1.700		
L2	1.310		
L3	1.625		
L4	0.150		
L5	0.530		
PKG CODE: F203A5F+1			

maxim integrated™

TITLE:

PACKAGE OUTLINE, 20L, FC2QFN PKG., 3.5X5.0X0.65mm

APPROVAL	PACKAGE OUTLINE NO.	REV.
---	21-100124	C / 1