



TOP VIEW



BOTTOM VIEW



SIDE VIEW

DIMENSIONS	
A	0.50±0.05
A1	0.19±0.03
A2	0.31 REF
A3	0.040 BSC
b	0.25±0.03
D1	0.40 BSC
E1	0.93 BSC
SD	0.20 BSC
SE	0.47 BSC

PKG CODE	E	D	DEPOPULATED BUMPS
N40D1+1	1.619±0.025	0.933±0.025	NONE

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. TERMINAL PITCH IS DEFINED BY TERMINAL CENTER TO CENTER VALUE.
3. OUTER DIMENSION IS DEFINED BY CENTER LINES BETWEEN SCRIBE LINES.
4. MARKING SHOWN IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
5. TOLERANCE IS ± 0.02 UNLESS SPECIFIED OTHERWISE.
6. FRONT - SIDE FINISH CAN BE EITHER BLACK OR CLEAR.
7. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE EU ROHS COMPLIANT WITHOUT EXEMPTION AND Pb-FREE.
8. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.
9. PACKAGE CODE: W40D1+1

-DRAWING NOT TO SCALE-

	maxim integrated™	TITLE: PACKAGE OUTLINE, 4 BUMPS WLP		
		APPROVAL SAURABH ATHAVALE 05/29/13	DOCUMENT CONTROL NO. 21-0723	REV. A 1/1