






TOP VIEW



SIDE VIEW

	SYMBOL	MIN	NOM	MAX
TOTAL THICKNESS	A	0.5	0.55	0.6
STAND OFF	A1	0	0.02	0.05
MOLD THICKNESS	A2	---	0.4	---
L/F THICKNESS	A3	0.152 REF		
LEAD WIDTH	b	0.2	0.25	0.3
	b1	0.11	0.16	0.21
BODY SIZE	X	2.5 BSC		
	Y	2.5 BSC		
LEAD PITCH	e	0.5 BSC		
	e1	0.3 BSC		
LEAD LENGTH	L	0.3	0.4	0.5
	L1	0.35	0.4	0.45
	L2	1.05	1.1	1.15
PACKAGE EDGE TOLERANCE	aaa	0.1		
MOLD FLATNESS	ccc	0.1		
COPLANARITY	eee	0.05		
LEAD OFFSET	bbb	0.1		



BOTTOM VIEW

NOTES

1. REFER TO JEDEC MO-220
2. COPLANARITY APPLIES TO LEADS, CORNER LEADS AND DIE ATTACH PAD
3. BAN TO USE THE LEVEL 1 ENVIRONMENT-RELATED SUBSTANCES OF JCET SPECS.
4. FINISH: Cu/EP • Sn8~20s
5. MAXIM PKG CODE : F122A2F+2
6. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.



TITLE:
PACKAGE OUTLINE, 12L FC2QFN
2.5x2.5x0.55mm

APPROVAL

DOCUMENT CONTROL NO.
21-100406

REV.
B

1/1

-DRAWING NOT TO SCALE-