



| DIM | INCHES | | MILLIMETERS | |
|----------------------------------|------------|-----------|-------------|-----------|
| | MIN | MAX | MIN | MAX |
| A | — | 0.043 | — | 1.10 |
| A1 | 0.002 | 0.006 | 0.05 | 0.15 |
| A2 | 0.030 | 0.037 | 0.75 | 0.95 |
| b | 0.010 | 0.014 | 0.25 | 0.36 |
| c | 0.005 | 0.007 | 0.13 | 0.18 |
| D | 0.114 | 0.122 | 2.90 | 3.10 |
| e | 0.0256 BSC | | 0.65 BSC | |
| E | 0.114 | 0.122 | 2.90 | 3.10 |
| H | 0.188 | 0.198 | 4.78 | 5.03 |
| L | 0.016 | 0.026 | 0.41 | 0.66 |
| α | 0° | 6° | 0° | 6° |
| S | 0.0207 BSC | | 0.5250 BSC | |
| PKG. CODES: | | | | |
| U8+1; U8+3; U8CN+1; U8+4; U8MS+5 | | | | |



FRONT VIEW

SIDE VIEW

NOTES:

1. D&E DO NOT INCLUDE MOLD FLASH.
2. MOLD FLASH OR PROTRUSIONS NOT TO EXCEED 0.15MM (.006").
3. CONTROLLING DIMENSION: MILLIMETERS.
4. COMPLIES TO JEDEC MO-187, LATEST REVISION, VARIATION AA.
5. MARKING SHOWN IS FOR PKG. ORIENTATION ONLY.
6. ALL DIMENSIONS APPLY TO BOTH LEADED (–) AND PbFREE (+) PKG. CODES.

—DRAWING NOT TO SCALE—

| | |
|---|---------------------------------|
|  ANALOG DEVICES | |
| TITLE: PACKAGE OUTLINE, 8L uMAX/uSOP | |
| APPROVAL ROHINI KESAVAN | DOCUMENT CONTROL NO. 21-0036 |
| REV. N | 1/1 |

REVISION HISTORY

TITLE: PACKAGE OUTLINE, 8L UMAX/USOP

DOCUMENT I.D.
21-0036

REVISION N

PAGE
2

