





		SYMBOL	MIN	NOM	MAX
TOTAL THICKNESS		A	0.8	0.85	0.9
STAND OFF		A1	0	0.035	0.05
MOLD THICKNESS		A2	---	0.65	---
L/F THICKNESS		A3	0.203 REF		
LEAD WIDTH		b	0.2	0.25	0.3
BODY SIZE	X	D	8 BSC		
	Y	E	8 BSC		
LEAD PITCH		e	0.5 BSC		
EP SIZE	X	J	6.15	6.25	6.35
	Y	K	6.15	6.25	6.35
LEAD LENGTH		L	0.35	0.4	0.45
		L1	0.3	0.4	0.45
PACKAGE EDGE TOLERANCE		aaa	0.1		
MOLD FLATNESS		bbb	0.1		
COPLANARITY		ccc	0.08		
LEAD OFFSET		ddd	0.1		
EXPOSED PAD OFFSET		eee	0.1		
HALF-CUT DEPTH		R	0.075	---	---
HALF-CUT WIDTH		S	---	---	0.075

NOTES

1. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
2. COPLANARITY APPLIES TO LEADS, CORNER LEADS AND DIE ATTACH PAD.
3. TOTAL THICKNESS NOT INCLUDE SAW BURR.
4. STEP CUT TYPE.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PARTS.
7. PACKAGE CODES:K4788Y+1C



TITLE:
PACKAGE OUTLINE, 47L, SAWN QFN-CU
8X8X0.9mm

APPROVAL	DOCUMENT CONTROL NO. 21-100593	REV. A	1/1
----------	-----------------------------------	-----------	-----

-DRAWING NOT TO SCALE-